

Plug socket
MSSD-EB-S-M14
Part number: 192745



Data sheet

Feature	Value
Frequency of connection	10
Type of mounting	On solenoid valve via M2.5 central screw
Mounting position	optional
Product weight	17 g
Electrical connection	4-pin Socket Type C
Cable diameter	4 mm...6 mm
Nominal cross section conductor	0.25 mm ² ...0.5 mm ²
Degree of protection	IP67 To IEC 60529
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA
Housing colour	Black