

Plug socket MSSD-C-S-M16

Part number: 192748



Data sheet

Feature	Value
Frequency of connection	10
Type of mounting	On solenoid valve via M3 central screw
Mounting position	optional
Product weight	38 g
Electrical connection	4-pin Socket Type A
Cable diameter	5.5 mm...8 mm
Nominal cross section conductor	0.5 mm ² ...1 mm ²
Degree of protection	IP67 To IEC 60529
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA
Housing colour	Black