

Stop element YSRWJ-8-14-A

Part number: 192966

FESTO



Data sheet

Feature	Value
Size	8
Stroke	14 mm
Cushioning	Self-adjusting Soft characteristic curve
Mounting position	optional
Fine adjustment	0.03 mm
Position detection	Via proximity switch
Max. impact speed	3 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	14 mm
Max. stop force	500 N
Max. energy consumption per stroke	3 J
Max. energy consumption per hour	21000 J
Max. residual energy	0.02 J
Reset force	3.5 N
Product weight	110 g
Type of mounting	Via lock nut
Material seals	NBR
Material housing	Brass Nickel-plated
Material piston rod	High-alloy steel