

Clevis foot
CRLBN-40
Part number: 195867



Data sheet

Feature	Value
Size	40
Mounting position	optional
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	185 g
Note on materials	RoHS-compliant
Material mounting	High-alloy stainless steel
Material bolt	High-alloy stainless steel
Material lock	High-alloy stainless steel