

Manifold
MHA2-PR8-3-M5
Part number: 197450



Data sheet

Feature	Value
Max. number of valve positions	8
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Mounting method for sub-base	With through-hole With H-rail
Mounting method for valve	Via female thread
Pneumatic connection, port 1/33	M7
Pneumatic connection, port 2	M5
Pneumatic connection, port 3/11	M7
Material sub-base	Wrought aluminium alloy