

Spiral plastic tubing PPS-4-7,5-1/4-BL

Part number: 19798

FESTO



Data sheet

| Feature | Value |
|--|---|
| Working length | 7.5 m |
| Outside diameter | 6.3 mm |
| Block length | 0.34 m |
| Inside diameter | 4.7 mm |
| Winding diameter | 75 mm |
| Number of turns | 44 |
| Temperature-dependent operating pressure | -0.95 bar...21.2 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -30 °C...80 °C |
| Nominal torque | 11 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 249 g |
| Pneumatic connection, port 1 | Male thread G1/4 |
| Pneumatic connection, port 2 | Male thread G1/4 |
| Colour | Blue |
| Material connecting thread | Brass |
| Note on materials | RoHS-compliant |
| Material buckling protection | Steel Galvanised |
| Material tubing | PA12-P |