

**Union nut**  
**MCK-PK-3**  
Part number: 205254



**Data sheet**

| Feature                                       | Value                                                                            |
|-----------------------------------------------|----------------------------------------------------------------------------------|
| Size                                          | Female thread M6x0.75                                                            |
| Operating pressure complete temperature range | -0.095 MPa...1.2 MPa<br>-0.95 bar...12 bar<br>-13.775 psi...174 psi              |
| Corrosion resistance class CRC                | 2 - Moderate corrosion stress                                                    |
| LABS (PWIS) conformity                        | VDMA24364-B2-L                                                                   |
| Ambient temperature                           | -10 °C...60 °C                                                                   |
| Pneumatic connection, port 1                  | For tubing outer diameter of 4 mm<br>For barbed fitting I.D. 3 mm with union nut |
| Material union nut                            | Wrought aluminium alloy, anodised                                                |
| Note on materials                             | RoHS-compliant                                                                   |