

Self-aligning rod coupler CRFK-M12X1,25

Part number: 2305779

FESTO



Data sheet

Feature	Value
Size	M12x1.25
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-20 °C...100 °C
Max. load capacity	1.5 kN
Product weight	230 g
Note on materials	RoHS-compliant
Material housing	High-alloy stainless steel
Material threaded bolt	High-alloy stainless steel
Material cap	EPDM
Material nut	High-alloy stainless steel