

Clamping sleeve
EAMH-60-6.35-C18.1
Part number: 2428516



Data sheet

Feature	Value
Size	60
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	1.46 kgmm ²
Product weight	36 g
Note on materials	RoHS-compliant