


Axial kit
EAMM-A-D50-70A-S1
Part number: 2734287



Data sheet

Feature	Value
Nominal length	69.2 mm
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transmittable torque	17 Nm
Product weight	740 g
Interface code, actuator	D50
Interface code, motor in	70A
Note on materials	RoHS-compliant