

# Parallel kit EAMM-U-110-D50-60G-120

Part number: 2797368

FESTO



## Data sheet

| Feature                               | Value                 |
|---------------------------------------|-----------------------|
| Size                                  | 110                   |
| Mounting position                     | optional              |
| Gear unit ratio                       | 1:1                   |
| Max. rotational speed                 | 5000 rpm              |
| LABS (PWIS) conformity                | VDMA24364 zone III    |
| Storage temperature                   | -25 °C...60 °C        |
| Relative air humidity                 | 0 - 95%               |
| Degree of protection                  | IP40                  |
| Ambient temperature                   | -10 °C...60 °C        |
| Mass moment of inertia                | 799 kgmm <sup>2</sup> |
| Frictional torque independent of load | 0.3 Nm                |
| Transmittable torque                  | 25 Nm                 |
| Product weight                        | 5290 g                |
| Interface code, actuator              | D50B                  |
| Interface code, motor in              | 60G                   |
| Note on materials                     | RoHS-compliant        |