

# Barbed elbow fitting LCN-M3-PK-2-B

Part number: 30491

**FESTO**



## Data sheet

Feature	Value
Nominal size	1.3 mm
Type of seal on screwed plug	Sealing ring
Operating pressure complete temperature range	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...60 °C
Pneumatic connection, port 1	Male thread M3
Pneumatic connection, port 2	For tubing outer diameter of 3 mm
Note on materials	RoHS-compliant
Material housing	Die-cast zinc High-alloy stainless steel