

Right angle clevis foot LQG-32

Part number: 31768



Data sheet

Feature	Value
Size	32
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...150 °C
Max. load capacity	0.9 kN
Product weight	301 g 10.61 oz
Note on materials	RoHS-compliant
Material mounting	Stainless steel casting
Material bolt	Case-hardened steel
Material lock	Spring steel