

Pressure gauge MA-40-16-1/8

Part number: 345395

FESTO



Data sheet

Feature	Value
Indicating range	0 bar...16 bar 0 psi...232 psi
Conforms to standard	EN 837-1
Nominal size of pressure gauge	40
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Design	Bourdon tube pressure gauge
Type of mounting	In-line installation
Operating medium	Inert gases Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Alternating load factor	0.66
Measurement accuracy class	2.5
Degree of protection	IP43
Media temperature	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Position of connection	Centred, rear side
Pneumatic connection	G1/8
Material in contact with the medium	Brass
Material screwed plug	Brass
Material housing	ABS
Material screen	PS
Housing colour	Black

Feature	Value
Product weight	60 g
Scale	Double scale Bar (outside scale) psi (inner scale)