

Exhaust air flow control valve GRE-3/8-NPT

Part number: 35311

FESTO



Data sheet

Feature	Value
Valve function	Sound pressure control function
Selection of additional functions	With silencer
Pneumatic connection, port 1	NPT3/8-18
Adjustment component	Slotted head screw
Type of mounting	Screw-in
Standard flow rate 0.6->0 MPa (6->0 bar, 87->0 psi)	3 l/min...2000 l/min
Operating pressure	0 bar...10 bar
Ambient temperature	-10 °C...70 °C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...70 °C
Note on materials	RoHS-compliant