

Solenoid coil VACC-S18-70-K5-3-U2D

Part number: 3546949

FESTO



Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Switching position indicator	no
Duty cycle	100%
Insulation material class	H
Characteristic coil data	220 V DC: 7.0 W
Permissible voltage fluctuations	-15%/+10%
CE mark (see declaration of conformity)	To EU Low Voltage Directive
Explosion protection certification outside the EU	Class I, Div. 2 (CA) Class I, Div. 2 (US)
Explosion protection	Class I, Div. 2 (CA) Class I, Div. 2 (US)
Explosion ambient temperature	T4A, 120 °C: -25 °C ≤ Ta ≤ +80 °C
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Product weight	1700 g
Electrical connection	Terminal box, cable entry thread NPT1/2
Note on materials	RoHS-compliant
Material solenoid coil	Wrought aluminium alloy Grey cast iron