

**Coupling piece**  
**KSZ-M12X1,25**  
Part number: 36126

**FESTO**



**Data sheet**

Feature	Value
Size	M12x1.25
Mounting position	optional
Threaded connection	Female thread M12x1.25
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	1.5 kN
Product weight	180 g
Note on materials	RoHS-compliant
Material mounting	Steel Galvanised
Material thread piece	Steel Galvanised