

Coupling piece
KSZ-M16X1,5
Part number: 36127

FESTO



Data sheet

| Feature | Value |
|----------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Size | M16x1.5 |
| Mounting position | optional |
| Threaded connection | Female thread M16x1.5 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical plug connectors and coils |
| Ambient temperature | -40 °C...150 °C |
| Max. load capacity | 4 kN |
| Product weight | 246 g |
| Note on materials | RoHS-compliant |
| Material mounting | Steel Galvanised |
| Material thread piece | Steel Galvanised |