

# Coupling piece KSZ-M20X1,5

Part number: 36128

FESTO



## Data sheet

Feature	Value
Size	M20x1.5
Mounting position	optional
Threaded connection	Female thread M20x1.5
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	9 kN
Product weight	418 g
Note on materials	RoHS-compliant
Material mounting	Steel Galvanised
Material thread piece	Steel Galvanised