

# Check valve H-M5

Part number: 3671

FESTO



## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | Non-return function  |
| Pneumatic connection, port 1                          | M5   |
| Pneumatic connection, port 2                          | M5   |
| Type of mounting                                      | In-line installation   |
| Standard nominal flow rate (standardised to DIN 1343) | 115 l/min  |
| Operating pressure                                    | 0.04 MPa...0.8 MPa<br>0.4 bar...8 bar  |
| Ambient temperature                                   | -10 °C...60 °C   |
| Material housing                                      | Brass  |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:...]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity                                | VDMA24364-B2-L   |
| Media temperature                                     | -10 °C...60 °C   |
| Note on materials                                     | RoHS-compliant   |
| Material seals  | NBR  |