

# Metal braided shielded hose PX-6

Part number: 4094

FESTO

Products to be discontinued. Available until 2011.



## Data sheet

Feature	Value
Outside diameter	9 mm
Bending radius relevant for flow rate	30 mm
Inside diameter	6 mm
Temperature dependent operating pressure	0 ... 12 bar
Ambient temperature	-20 ... 80 °C
Product weight according to length	0.14 kg/m
Colour	silver
Shore hardness	75 +/- 5
Materials note	Contains PWIS substances
Materials information for tubing	NBR