

Pressure indicator
OH-22-RT
Part number: 4131

FESTO



Data sheet

Feature	Value
Mounting position	optional
Operating pressure	1.4 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...45 °C
Ambient temperature	-10 °C...45 °C
Product weight	25 g
Type of mounting	Installation into control panel in Ø22.5
Pneumatic connection	G1/8
Note on materials	RoHS-compliant