

Sub-base
VABS-S7-RB-B-N14-VDE1-R12
Part number: 4727331

FESTO



Data sheet

Feature	Value
Mounting position	optional
Pilot air supply	External Internal
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [:-::-]
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Type of mounting	With through-hole
Pilot air port 12	1/4 NPT
Pneumatic connection, port 1	1/4 NPT
Pneumatic connection, port 2	VDI/VDE 3845 (NAMUR)
Pneumatic connection, port 3	1/4 NPT
Note on materials	RoHS-compliant
Material sub-base	Ematal coated aluminium
Material seals	NBR