

Drive shaft adapter DARF-Q11-32

Part number: 4835940

FESTO



Data sheet

Feature	Value
Size	32
For piston diameter	Diameter 32
Design	Drive shaft
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	287 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Material screws	Nickel-plated steel