

**Manifold**  
**MHA3-PR6-3-1/8**  
Part number: 525223



**Data sheet**

| Feature                         | Value                            |
|---------------------------------|----------------------------------|
| Max. number of valve positions  | 6                                |
| Corrosion resistance class CRC  | 2 - Moderate corrosion stress    |
| LABS (PWIS) conformity          | VDMA24364-B1/B2-L                |
| Mounting method for sub-base    | With through-hole<br>With H-rail |
| Mounting method for valve       | Via female thread                |
| Pneumatic connection, port 1/33 | G1/4                             |
| Pneumatic connection, port 2    | Female thread G1/8               |
| Pneumatic connection, port 3/11 | G1/4                             |
| Material sub-base               | Wrought aluminium alloy          |