

Manifold
MHA3-PR10-3-1/8
Part number: 525225



Data sheet

| Feature | Value |
|---------------------------------|----------------------------------|
| Max. number of valve positions | 10 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Mounting method for sub-base | With through-hole With H-rail |
| Mounting method for valve | Via female thread |
| Pneumatic connection, port 1/33 | G1/4 |
| Pneumatic connection, port 2 | Female thread G1/8 |
| Pneumatic connection, port 3/11 | G1/4 |
| Material sub-base | Wrought aluminium alloy |