

Bus connection
FBSD-KL-2X5POL
Part number: 525635

FESTO



Data sheet

Feature	Value
Type of mounting	With through-hole
Mounting position	optional
Product weight	20 g
Electrical connection	5-pin/5-pin Angled socket/screw terminal
Operational voltage range DC	24 V
Permissible current load	12 A
Connection cross section	0.2 mm ² ...2.5 mm ²
Degree of protection	IP20
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA
Housing colour	Black
Material electrical contact	Bronze Bronze