

Sealing ring OK-1/2

Part number: 531774

FESTO



Data sheet

Feature	Value
Based on standard	ISO 16030
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Tightening by hand at room temperature	yes
Nominal torque	14 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	0.6 g
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Material stops	Reinforced PA
Material seals	TPE-U(PU)