

Plug

FBS-SUB-9-GS-DP-B

Part number: 532216

FESTO



Data sheet

Feature	Value
Width	20 mm
Height	62 mm
Length	61 mm
Protocol	PROFIBUS
Operator controls	DIL switch
Additional functions	Switching off of outgoing fieldbus segment
Product weight	60 g
Field bus interface	2x 2 spring-loaded terminals
Permissible cable diameter	5 mm...10 mm
Degree of protection	IP65 IP67 In assembled state To IEC 60529
Ambient temperature	0 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Material union nut	Brass
Material screws	Steel
Material seals	NBR