

Electrical module

VMPA2-FB-EMS-D2-4

Part number: 543332

FESTO



Data sheet

Feature	Value
Diagnosis	Condition monitoring Wire break per solenoid coil Short circuit of valves Undervoltage of valves
Max. number of valve positions	2
Max. number of valve coils	4
Internal current consumption, load voltage	3 mA
Internal current consumption, operating voltage	8 mA
Nominal pick-up current per solenoid coil	99 mA up to 24 ms
Nominal current with current reduction	18 mA after 24 ms
Corrosion resistance class CRC	1 - Low corrosion stress (when installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	20 g
Material housing	POM
Note on materials	RoHS-compliant