

# Multi-pin node VABE-S6-1LF-C-M1-C36M

Part number: 543412

FESTO



## Data sheet

Feature	Value
Based on standard	EN 61984
Mounting position	optional
Max. number of valve positions	16 with bistable valves 32 with monostable valves
Max. resultant current	6 A
Nominal operating voltage DC	24 V
Immunity to surge	1.5 kV
Current rating at 40° C	1 A
Pollution degree	3
Permissible voltage fluctuations	+/- 10 %
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C...50 °C
Product weight	545 g
Electrical control	Multi-pin plug
Electrical connection	Socket/terminal strip
Material cover	PA
Material housing	Die-cast aluminium