

Pressure gauge PAGN-26-10-P10

Part number: 543488

FESTO



Data sheet

Feature	Value
Indicating range	0 bar...10 bar 0 psi...145 psi
Nominal size of pressure gauge	26
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Design	Bourdon tube pressure gauge without measuring mechanism
Type of mounting	In-line installation
Operating medium	Inert gases Neutral fluids
Note on operating and pilot medium	No acetylene No oxygen
Operating pressure	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Alternating load factor	0.66
Measurement accuracy class	4
Degree of protection	IP43 NEMA 4
Media temperature	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Position of connection	Centred, rear side
Pneumatic connection	Cartridge 10 mm
Material in contact with the medium	Brass
Material screwed plug	Brass
Material housing	PA
Material screen	PS
Housing colour	Black
Product weight	15 g

Feature	Value
Scale	Double scale Bar (outside scale) psi (inner scale)