


Hood NECV-S1W37

Part number: 545974

FESTO



Data sheet

Feature	Value
Area of application	Only for multi-pin plug connection valve terminal VTSA/VTSA-F
Product weight	180 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connector system	Sub-D
Electrical connection 1, number of connections/cores	37
Electrical connection 1, used connections/cores	37
Electrical connection 1, type of mounting	3x screw M4
Electrical connection 2, connector system	Crimp contacts
Operational voltage range DC	0 V...30 V
Current rating at 40° C	2 A
Immunity to surge	1 kV
Cable fitting	M20x1.5
Cable diameter	5 mm...13 mm
Nominal cross section conductor	0.08 mm ² ...0.5 mm ²
Degree of protection	IP65 NEMA 4
Note on degree of protection	In assembled state
Ambient temperature	-5 °C...50 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material housing	PA