


Basic valve LFMA-D-MIDI-A-U

Part number: 546446

FESTO



Data sheet

Feature	Value
Series	D
Size	Midi
Design	Fibre filter
Grade of filtration	0.01 µm
Condensate drain	Fully automatic
Operating pressure	0.2 MPa...1.2 MPa 2 bar...12 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:4] Inert gases
Air purity class at output	Compressed air to ISO 8573-1:2010 [3:4:2] Inert gases
Filter efficiency	99.9999 %
Bowl guard	Metal bowl guard
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	33.8 °F...140 °F
Ambient temperature	14 °F...140 °F
Filter efficiency, fine particles	99995 %
MPPS	0.05 µm
Filter efficiency MPPS	99.95 %
Residual oil content	2.7E-07 oz/yd³
Filter efficiency, oil aerosol	99 %
Type of mounting	In-line installation With accessories Either:
Mounting position	Vertical +/-5°
Material housing	Die-cast zinc
Material filter	Borosilicate fibre
Material bowl	PC
Note on materials	RoHS-compliant
Product weight	22.8 oz