


Basic valve LFR-D-7-MAXI

Part number: 546470

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Actuator lock	Rotary knob with detent
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	40 μm
Condensate drain	Manually rotating
Design	Filter regulator without pressure gauge
Max. condensate volume	2.7 fl oz (US)
Bowl guard	Metal bowl guard
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	Prepared for G1/4
Operating pressure	0.1 MPa...1.6 MPa 1 bar...16 bar
Pressure regulation range	0.5 bar...7 bar
Max. pressure hysteresis	6 psi
Standard nominal flow rate (standardised to DIN 1343)	1493 cfm
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	14 °F...140 °F
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:8:4] Inert gases
Media temperature	14 °F...140 °F
Ambient temperature	14 °F...140 °F
Product weight	51.5 oz
Type of mounting	In-line installation With accessories Either:
Note on materials	RoHS-compliant
Material housing	Die-cast zinc
Material bowl	PC