

Solenoid coil

MD-2-230VAC-PA

Part number: 549905

FESTO



Data sheet

| Feature | Value |
|--|--|
| Type of actuation | Electric |
| Mounting position | optional |
| Duty cycle | 100% |
| Power factor (cos phi) | 0.7 |
| Characteristic coil data | 230 V AC: 50/60 Hz, pick-up power 14.5 VA, holding power 10.5 VA |
| Permissible frequency fluctuations | +/- 10% |
| Permissible voltage fluctuations | +/- 10 % |
| CE mark (see declaration of conformity) | To EU Low Voltage Directive |
| UKCA marking (see declaration of conformity) | To UK regulations for electrical equipment |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Degree of protection | IP65 |
| Ambient temperature | -20 °C...50 °C |
| Max. tightening torque for fitting | 0.5 Nm |
| Product weight | 110 g |
| Electrical connection | To DIN EN 175301-803 |
| Type of mounting | Via knurled nut |
| Note on materials | RoHS-compliant |
| Material solenoid coil | Duroplast Copper Steel |
| Material winding | Copper |