


Plug socket **MSSD-N**

Part number: 550067

FESTO



Data sheet

Feature	Value
Based on standard	EN 175301-803
Cable outlet	Angled
Product weight	30 g
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, connector system	Plug pattern type A to EN 175301-803
Electrical connection 1, number of connections/cores	3
Electrical connection 1, type of mounting	On solenoid valve via M3 central screw
Electrical connection 2, connector system	Screw terminal
Operational voltage range DC	0 V...24 V
Operational voltage range AC	0 V...250 V
Current rating at 40° C	16 A
Cable fitting	M20x1.5
Cable diameter	8 mm...10 mm
Nominal cross section conductor	1.5 mm ²
Degree of protection	IP65
Note on degree of protection	In assembled state
Ambient temperature	-25 °C...80 °C
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Housing colour	Black
Material screws	Steel
Material seals	VMQ