

# Silencer U-1/2-BR

Part number: 552422

FESTO



## Data sheet

| Feature                            | Value  |
|------------------------------------|--|
| Mounting position                  | optional   |
| Operating pressure                 | 0 MPa...1 MPa<br>0 bar...10 bar  |
| Flow rate to atmosphere            | 10600 l/min  |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:-:-]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Sound pressure level               | 80 dB(A)   |
| Ambient temperature                | -10 °C...70 °C   |
| Product weight                     | 75 g   |
| Pneumatic connection               | G1/2   |
| Material shock absorber insert     | PE   |
| Material housing                   | Die-cast aluminium   |