

# Bellows kit DADB-S1-25-S10-50

Part number: 553421

**FESTO**



## Data sheet

Feature	Value
Outside diameter	29 mm
Size	25
Stroke range	10 mm...50 mm
Piston rod extension	22 mm
Design	Round Bellows kit With ducted exhaust air
Mounting position	optional
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Media resistance	Dust Chips Oils Grease Petrol
Ambient temperature	-10 °C...80 °C
Product weight	19 g
Type of mounting	Via threaded pin Via female thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel