

# Plastic tubing PUN

Part number: 553573

FESTO



## Data sheet

Feature	Value
Outside diameter	3 mm...16 mm
Inside diameter	2 mm...11 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.95 bar...30 bar
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See supplementary material information
Ambient temperature	-35 °C...60 °C
Colour	Blue Brown Yellow Green Natural Red Black Silver Translucent blue Translucent yellow Translucent green Translucent red Translucent black White
Note on materials	RoHS-compliant
Material tubing	TPE-U(PU)