

Plastic tubing PAN

Part number: 553610

FESTO



Data sheet

Feature	Value
Outside diameter	4 mm...16 mm
Inside diameter	2.5 mm...12 mm
Conforms to standard	DIN 73378-PA12-PHL
Temperature-dependent operating pressure	-0.95 bar...35 bar
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Mineral oil
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-60 °C...100 °C
Colour	Blue Brown Yellow Green Natural Red Black Silver White
Note on materials	RoHS-compliant
Material tubing	PA12-P TPE-A