

Plastic tubing
PAN-8X1,25-SI-400
Part number: 553890

FESTO



Data sheet

Feature	Value
Outside diameter	8 mm
Flow-relevant bending radius	43 mm
Inside diameter	5.9 mm
Min. bending radius	22 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...1.5 MPa -0.95 bar...15 bar -13.775 psi...217.5 psi
Approval	German Technical Control Board (TÜV)
Maritime classification	See certificate
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight according to length	0.024 kg/m
Pneumatic connection	For push-in connector O.D. 8 mm For barbed fitting inside diameter of 6 mm with union nut For barbed fitting inside diameter of 6 mm
Colour	Silver
Shore hardness	D 55 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-A