


Angled connection plate VABF-S2-2-A1G2-N12

Part number: 555703

FESTO



Data sheet

| Feature | Value |
|------------------------------------|--|
| Construction width | 58.1 mm |
| Based on standard | ISO 5599-2 |
| Mounting position | optional |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP65 NEMA 4 |
| Ambient temperature | -5 °C...50 °C |
| Product weight | 359 g |
| Type of mounting | With through-hole |
| Note on materials | RoHS-compliant |
| Material housing | Wrought aluminium alloy |