

Plastic tubing PLN-12X1,75-SI

Part number: 558215

FESTO



Data sheet

Feature	Value
Outside diameter	12 mm
Flow-relevant bending radius	65 mm
Inside diameter	8.4 mm
Min. bending radius	23 mm
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Note on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See supplementary material information
Ambient temperature	-30 °C...80 °C
Product weight according to length	0.054 kg/m
Pneumatic connection	For push-in connector outside diameter of 12 mm
Colour	Silver
Note on materials	RoHS-compliant
Material tubing	PE