

Push-in L-connector NPQM-L-Q10-E-P10

Part number: 558779

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	9 mm
Design	L-shape Push-pull principle
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...70 °C
Product weight	29.5 g
Pneumatic connection, port 1	For tubing outer diameter of 10 mm
Pneumatic connection, port 2	For tubing outside diameter of 10 mm
Note on materials	RoHS-compliant
Material housing	Brass, nickel-plated
Material tubing seal	NBR