

Push-in T-connector NPQM-T-Q8-S8-P10

Part number: 558793

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 5.5 mm |
| Design | T-shape Push-pull principle |
| Size of pack | 10 |
| Operating pressure complete temperature range | -0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...70 °C |
| Product weight | 29 g |
| Pneumatic connection, port 1 | Push-in sleeve Ø 8 mm |
| Pneumatic connection, port 2 | For tubing outside diameter of 8 mm |
| Note on materials | RoHS-compliant |
| Material housing | Brass, nickel-plated |
| Material tubing seal | NBR |