

Multiple distributor NPQM-LFK-G14-Q8-P10

Part number: 558841

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	6.5 mm
Type of seal on screwed plug	Sealing ring
Design	L-shape, dual, F-outlet Push-pull principle
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...70 °C
Nominal torque	7.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	69.5 g
Type of mounting	Internal hexagon, size 5 mm
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	For tubing outside diameter of 8 mm
Note on materials	RoHS-compliant
Material housing	Brass, nickel-plated
Material hollow bolt	Nickel-plated brass
Material tubing seal	NBR