

Manifold sub-base VABV-S2-2S-N12-T2

Part number: 560843



Data sheet

Feature	Value
Grid dimension	59 mm
Terminal type	44
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	610 g
Pneumatic connection, port 2	1/2 NPT
Pneumatic connection, port 4	1/2 NPT
Note on materials	RoHS-compliant
Material plate	Die-cast aluminium