

# Sub-base VMPAL-AP-10-QS1/4"-1

Part number: 560999

FESTO



## Data sheet

| Feature                            | Value  |
|------------------------------------|--|
| Width                              | 10.7 mm  |
| Length                             | 107.3 mm   |
| Grid dimension                     | 10.7 mm  |
| Valve size                         | 10 mm  |
| Max. number of valve positions     | 1  |
| Flow direction                     | Reversible   |
| Valve terminal structure           | Valve sizes can be mixed   |
| Max. number of valve coils         | 1  |
| Operating pressure                 | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar   |
| Pilot pressure                     | 0.3 MPa...0.8 MPa<br>3 bar...8 bar   |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 3 - high corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Ambient temperature                | -5 °C...50 °C  |
| Product weight                     | 30 g   |
| Pneumatic connection, port 2       | For tubing outside diameter of 1/4"  |
| Pneumatic connection, port 4       | For tubing O.D. 1/4"   |
| Note on materials                  | RoHS-compliant   |
| Material sub-base                  | PA-reinforced  |