

**Distributor**  
**FR-4-3/8**  
Part number: 561602

**FESTO**



**Data sheet**

Feature	Value
Nominal size	16 mm
Mounting position	optional
Operating pressure complete temperature range	0 bar...16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Number of outputs	3
Number of supply lines	1
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Material housing	Wrought aluminium alloy Anodised